





(B) Outdoor Units
U-200PZH4E8, U-250PZH4E8

Unit: mm




When using a drain pipe, install the drain socket (field supply) onto the drain port. Seal the other drain port with the rubber cap.

①	Mounting hole (4-R6.5), anchor bolt : M10
②	Refrigerant tubing (liquid tube), flared connection ($\phi 12.7$)
③	Refrigerant tubing (gas tube), flared connection ($\phi 22.22$)
④	Refrigerant tubing port
⑤	Electrical wiring port ($\phi 13$)
⑥	Electrical wiring port ($\phi 22$)
⑦	Electrical wiring port ($\phi 27$)
⑧	Electrical wiring port ($\phi 35$)



A VIEW



Z VIEW

1-4. Dimensional Data


(A) Indoor Units

High Static Pressure Ducted Type S-200PE4E, S-250PE4E

Required Minimum Space for Installation and Service

(1) Dimensions of suspension bolt pitch and unit

Unit: mm



(2) Dimensions of indoor unit

Unit: mm

